

## DECLARATION OF COMPLIANCE Fluorodyne® II Filter Cartridges MCY Junior Style “W” Code

### Cartridge Part Number

MCY4440FSDWH4

This is a guide to the Part Numbering structure only. For specific options, please contact Pall.

Fluorodyne II Junior Style filter cartridges are intended for dosing flavor, color, aqueous ingredients and other critical solutions into food and beverage products. This filter is not suitable for the filtration of fatty foods.

The filter medium comprises a hydrophilic PVDF membrane.

An initial flush is recommended prior to use.

Issued	30 October 2015
Revised	15 January 2019
Expires	28 February 2021
Reference	FBDCFSDJENb
Page	1 of 3



Steven Bailey  
Quality Manager  
Pall Manufacturing (UK) Ltd., Ilfracombe

## Fluorodyne II Junior Style Filter Cartridges (“W” Code)

### Components

Filter Media	Hydrophilic polyvinylidene fluoride (PVDF) membrane
Cage, Core, and End Cap	Polypropylene
Adaptor	Polypropylene
O-ring Seal	Silicone Elastomer (H4)

### Declaration

Fluorodyne II “W” Code filter cartridges comprise of materials that meet regulatory and legislative requirements and guidelines for food contact in that:

### Europe

The “W” Code Fluorodyne II filter cartridges meet the requirements for food contact as detailed in European Regulation (EC) Number 1935/2004 in that:

- Our suppliers’ information indicates that the polymeric materials used to produce “W” Code Junior Style Fluorodyne II products are made from monomers and additives consistent with Annex I of Commission Regulation (EU) Number 10/2011, relating to plastic materials and articles intended to come into contact with foodstuffs (excluding seals).

Migration testing (OML) of the Fluorodyne II Junior Style filter has been performed, and meets migration criteria after flushing and in flow conditions at greater than 0.05 kg/hr per filter in:

Simulant A (10 % ethanol) for 2 hours up to 40 °C (104 °F),  
 Simulant B (3 % acetic acid) for 2 hours up to 40 °C (104 °F),  
 and Simulant D2 (95 % ethanol) for 2 hours up to 40 °C (104 °F),  
 under repeated use conditions

Additionally, migration testing of the filter components of Fluorodyne II filters have been performed and met migration criteria after flushing and in flow conditions in:

Simulant A (10 % ethanol) for 4 hours up to 100 °C (212 °F)  
 and 65 % ethanol for 4 hours up to 100 °C (212 °F).

#### Note:

This product contains materials that are subject to Specific Migration Limit (SML) requirements.  
 This product contains calcium stearate, which is approved as a direct food additive.

- Samples of the silicone elastomeric (H4) seal material formulation, typically used with the above part numbers, have been tested as 226 size seals for overall migration. Testing was conducted in distilled water, 3 % acetic acid and 20 % ethanol, under reflux conditions for 4 hours - repeat use. In respect of the overall migration limit for food contact elastomers according to the French requirements (given in Arrete of November 9th 1994 and published in Journal Officiel de la Republique Francaise, December 2nd 1994, p17029-17036) is 10 mg/dm<sup>2</sup>, data obtained with the rubber o-rings under the tested conditions was well within this limit.
- The volatile levels from samples of the silicone elastomer (H4) formulation, after heating at 200 °C for 4 hours, was found to be within the BfR section XV specification for this material.

Users should satisfy themselves that these materials are suitable for use in their specific food application.

## USA

The materials of construction meet the FDA requirements for food contact use as detailed in Code of Federal Regulations, 21 CFR paragraphs 170-199 in that:

- Our suppliers state that base polymer materials used by Pall to manufacture the "FSDW" filter membrane and polypropylene components of the above Pall product are listed in 21 CFR 170-199:
  - PVDF to 21 CFR section 177.2510 (Polyvinylidene fluoride resins) – excluding hydrophilicity
  - Polypropylene to 21 CFR section 177.1520 (Olefin polymers)
- Hydrophilicity -- Membrane was analyzed as per ASTM D2857-95 test methods for conformance to FDA specifications for a food contact substance. The membrane met the specifications for polyvinylidene fluoride resins as described in Title 21 of the U.S. Code of Federal Regulations 177.2510 paragraphs (a), (b), and (c) including acceptable heavy metals content. Additionally, no specified or known adjuvants were detected at a limit of 0.001%.
- Silicone Elastomeric seal materials to 21 CFR section 177.2600 (Rubber articles intended for repeated use, excluding milk and edible oils)

## Process Quality System

Site of Manufacture: Pall Manufacturing (UK) Ltd., Ilfracombe, UK on behalf of Pall International Sàrl.

The Quality Management System at Pall Manufacturing (UK) Ltd., Ilfracombe, is certified to ISO 9001:2015.

These products / product packaging carry a lot number / date code to facilitate traceability to suppliers' materials and Pall production records.

Pall Manufacturing (UK) Ltd. confirms that the product is manufactured in line with the principles of food contact materials GMP as detailed in Regulation 2023/2006

## Supplied in Europe by

Pall International Sàrl  
 Av. de Tivoli 3  
 Fribourg  
 Switzerland  
 CH-1700




### Pall Food and Beverage

New York - USA  
 +1 516 484 3600 telephone  
 +1 866 905 7255 toll free  
 foodandbeverage@pall.com

Visit us on the web at [www.pall.com](http://www.pall.com)

Pall Corporation has offices throughout the world. For Pall representatives in your area, please go to [www.pall.com/contact](http://www.pall.com/contact).

Because of developments related to products, systems and/or services described herein, the data and procedures are subject to change without notice. Please consult your Pall representative or visit [www.pall.com](http://www.pall.com) to verify that this information remains valid.

© Copyright 2019, Pall Corporation. Pall,  and Fluorodyne are trademarks of Pall Corporation. ® indicates a trademark registered in the USA.  
**Filtration. Separation. Solution.<sup>SM</sup>** mark of Pall Corporation.