

DECLARATION OF COMPLIANCE

Nexis® T Series Filter Cartridges

“W” Code

Cartridge Part Number

NXT U W 480

Table 1 Table 2 Table 3 Table 4

This is a guide to the part numbering structure only. For specific options, please contact Pall.

Table 1 : Removal Rating

| Code | Description |
|------|-------------|
| 3 | 3 µm |
| 5 | 5 µm |
| 10 | 10 µm |
| 20 | 20 µm |
| 30 | 30 µm |
| 40 | 40 µm |
| 50 | 50 µm |
| 75 | 75 µm |
| 100 | 100 µm |
| 150 | 150 µm |
| 200 | 200 µm |

Table 2 : Nominal Length

| Code | Description |
|-----------------------|-----------------|
| DOE Style Only | |
| 4 | 102 mm (4") |
| 5 | 127 mm (5") |
| 975 | 248 mm (9.75") |
| 9875 | 251 mm (9.875") |
| 10 | 254 mm (10") |
| 195 | 495 mm (19.5") |
| 20 | 508 mm (20") |
| 2925 | 753 mm (29.25") |
| 295 | 748 mm (29.5") |
| 30 | 762 mm (30") |
| 39 | 991 mm (39") |
| 395 | 1003 mm (39.5") |
| 40 | 1016 mm (40") |
| SOE Style only | |
| 10 | 254 mm (10") |
| 20 | 508 mm (20") |
| 30 | 762 mm (30") |
| 40 | 1016 mm (40") |

Table 3 : Adaptor

| Code | Description |
|-------|---|
| Blank | DOE - double open end with no End Caps |
| M3 | SOE - single open end with flat closed end and external 222 O-rings |
| M7 | SOE - single open end with fin end, 2 locking tabs and external 226 O-rings |
| M8 | SOE - single open end with fin end and external 222 O-rings |

Table 4 : O-ring Seal Material*

| Code | Description |
|------|---------------------------|
| S | Silicone Elastomer |
| E | Ethylene Propylene Rubber |


* For M3, M7 and M8 configurations only

Nexis T Series high efficiency deep bed filter cartridges are constructed using an advanced, microprocessor controlled CoLD Melt™ production process that permits the creation of multiple filtration zones within a single filter cartridge. The multi-zone design produces a gradient pore structure that effectively captures large particles in the outer sections of the filter cartridge while providing highly efficient and consistent removal of smaller particles in the inner sections.

CoLD Melt fiber technology has been selectively integrated into critical zones of the Nexis filter to enhance the retention, efficiency and mechanical strength of the cartridge. The interlocking and thermal bonding of support fibers with ultra-thin filtration fibers creates a rigid matrix that withstands dynamic operating conditions.

An initial flush is recommended prior to use.

Issued 1 May 2009
 Revised 28 February 2017
 Expires 28 February 2019
 Reference FBDCNEXISTENm
 Page 1 of 3



Gary W. Kehs
 Quality Manager
 Pall Timonium

Nexis T Series Filter Cartridges (“W” Code)

Components

| | |
|---------------------------|--|
| Filter Media | Polypropylene |
| Core, End Cap and Fin End | Polypropylene |
| Adaptor | Polypropylene |
| O-ring Seal | Silicone Elastomer (S) or Ethylene Propylene Rubber (E) |

Declaration

Nexis T Series “W” Code filter cartridges are comprised of materials that meet regulatory and legislative requirements and guidelines for food contact in that:

Europe

The “W” Code Nexis T Series filter cartridges meet the requirements for food contact as detailed in European Regulation (EC) Number 1935/2004 in that:

- Our suppliers information indicates that the polymeric materials used to produce “W” Code Nexis T Series filter cartridges are made from monomers and additives consistent with Annex I of Commission Regulation (EU) Number 10/2011 and its amendments, relating to plastic materials and articles intended to come into contact with foodstuffs (excluding seals).

Migration testing has been performed, and met migration criteria after flushing and in flow conditions in:

Simulant B (3% acetic acid) 2 hours at reflux

Simulant C (20% ethanol) 2 hours at reflux

Simulant D1 (50% ethanol) 2 hours at reflux

and

Water up to 70 °C (158 °F).

10% ethanol up to 70 °C (158 °F)

Note:

This product contains materials that are subject to Specific Migration Limit (SML) requirements (excluding DOE configurations).

This product contacts calcium stearate, which is approved as a direct food additive.

USA

The materials of construction meet the FDA requirements for food contact use as detailed in Code of Federal Regulations, 21 CFR paragraphs 170-199:

- Polypropylene to 21 CFR sections 177.1520 (Olefin polymers)
- Silicone Elastomer and Ethylene Propylene Rubber seal materials to 21 CFR section 177.2600 (Rubber articles intended for repeated use, excluding milk and edible oils).

Process Quality System

Site of Manufacture: Pall Timonium, USA

The Quality Management System at Pall Timonium is certified to ISO 9001:2008.

These products / product packaging carry a lot number / date code to facilitate traceability to suppliers' materials and Pall production records.

Supplied in Europe

Pall International Sàrl
Av. de Tivoli 3
Fribourg
Switzerland
CH-1700




Pall Food and Beverage

New York - USA
+1 516 484 3600 telephone
+1 866 905 7255 toll free
foodandbeverage@pall.com

Visit us on the web at www.pall.com

Pall Corporation has offices throughout the world. For Pall representatives in your area, please go to www.pall.com/contact.

Because of developments related to products, systems and/or services described herein, the data and procedures are subject to change without notice. Please consult your Pall representative or visit www.pall.com to verify that this information remains valid.

© Copyright 2017, Pall Corporation. Pall, , CoLD Melt and Nexis are trademarks of Pall Corporation. ® indicates a trademark registered in the USA. Filtration.Separation.Solution is a service mark of Pall Corporation.